
WHEEL BALANCERS Electronic wheel balancers with microprocessor


The Perfect Balance between Precision and Practicality





Ravaglioli

G3.150 **G**3.128NR



Impeccable precision:

automatic wheel data acquisition and laser blade

Practical design:

everything has a place, everything is in the right spot

Intuitive technology:

graphics and colors are studied to facilitate the use of the wheel balancer




Electronic wheel balancers with microprocessor with wheel stops automatically in both outside and inside unbalance position. Quick selection with internal data gauge. Automatic storage of distance and diameter.



Run-out measurement.

Rim Run-out measurement with internal data gauge.







Double led light and laser blade (with a laser line at 6 o'clock for adhesive weights) to properly and easily fit weight in the right position.





Modern balancing system to minimize wheel weights consumption.











AUTOMATIC STOP (IN)

Position locking.


Wheel stops automatically in both outside and inside unbalance position.










Technical data





G3.128NR





G3.150

	G3.128NR	G3.150
Min. rim diameter	10"	10"
Max. rim diameter	26"	26"
Min. rim width	1.5"	1.5"
Max. rim width	22"	22"
Max. wheel weight	70 kg	70 kg
Balancing accuracy +/-	1 g	1 g
Measuring time	6 s	6 s
Measuring speed	100 rpm	100 rpm
Power supply	230V/50-60/1ph	230V/50-60/1ph



Accessories

		G3.128NR	GP3.128NR	G3.150	G3.150S	GP3.150S	G3.150WS	GP3.150WS
000	GAR111 Passenger car cone set (ø 44 - 112 mm)	S	S	S	S	S	S	S
*0 0	GAR345 Quick nut	S	-	S	S	-	S	-
0	GAR351 Locking hub	-	S	-	-	S	-	S
	GAR112 Centering cone	Ο	0	ο	ο	Ο	Ο	0
_]	GAR306 Wheel width gauge	Ο	0	ο	S	S	-	-
T	GAR311 laser blade + LED light	Ο	0	Ο	S	S	S	S
	GAR315 Run-out sonar	ο	0	-	ο	ο	-	-
	GAR377 Run-out sonar	-	-	-	-	-	Ο	ο
	GAR332 Wheel width sonar	-	-	-	-	-	S	S
	GAR324 - GAR325 Wheel lift	Ο	0	Ο	Ο	Ο	0	0
TEq-Link	GAR358 Workshop connectivity software	0	0	0	0	0	0	0

S Standard

Optional



RAV Italy

Ravaglioli S.p.A.

Via Primo Maggio 3 Pontecchio Marconi 40037 Sasso Marconi BO

Section 1.39.051.6781511
Image: Hardware 1.39.051.846349
Image: Hardwar

RAV France RAV France SARL

4, Rue Longue Raie ZAC de la Tremblaie 91220 Le Plessis Pâté

Section 1.60.86.88.16
Section 1.60.86.82.04
Section 1.60.86.82.04
Section 1.60.86.82.04

RAV Germany BlitzRotary GmbH

Hüfinger Straße 55 78199 Bräunlingen Germany

Section 449.771.9233.0
Begin 449.771.9233.99
Section and the mathematical mathemat

RAV UK Vehicle Service Group UK Ltd

3 Fourth Avenue, Bluebridge Industrial Estate Halstead, Essex, CO9 2SY, UK

↔ +44.1787.477711
➡ +44.1787.477720
☑ rav@ravaglioli.com

DRJ19U(01)

Technical data and composition presented in this catalogue may vary. Pictures reproduced are only indicative. Member of VSG - Vehicle Service Group a - DOVER company

